

TONGA MID

TONGAMID

Upper	Suede Leather, Synthetic Nubuck
Lining	Membrane
Footbed	SJ foam footbed
Size range	EU 39-47 / UK 6.0-12.0 / US 6.5-13.0 JPN 25-31 / KOR 255-310
Sample weight	0.467 kg



NAV

Waterproof (WR)

Waterproof footwear prevents liquids to enter into the shoe.

Rubber outsole

Rubber outsoles provide versatile functions that make them suitable for many areas of application: excellent cut resistance, heat and cold resistance, high flexibility at cold temperatures, resistance against oil, fuel and many chemicals.

Environments:

Uneven surfaces, Wet environment

Maintenance instructions:

To extend the life of your shoes, we recommend to clean them regularly and to protect them with adequate products. Do not dry your shoes on a radiator, nor nearby a heat source.

Removable insole

Renew your insole at a regular base or use your own orthopedic insoles for a higher comfort.

Heel energy absorption

Heel energy absorption reduces the impact of jumps or running on the body of the wearer.